

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778936

Luminaire Tested: LER4D05D010-EC4DR300210IC9035-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR300210IC9035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 646.5 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778936

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P778936

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	159111	159111	159111
5°	154540	154363	154555
10°	133857	132916	133826
15°	87334	86867	86431
20°	43424	45061	43367
25°	21874	24670	21427
30°	8759	9546	7628
35°	4065	3897	3261
40°	1749	1948	1659
45°	1245	1537	1245
50°	429	1119	453
55°	240	467	254
60°	168	199	168
65°	109	109	109
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1537 cd/sqm



TEST NUMBER: P778936

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.8	28.3
10°-20°	294.4	45.5
20°-30°	127.2	19.7
30°-40°	29.0	4.5
40°-50°	10.0	1.5
50°-60°	2.4	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.4	93.5
0°-40°	633.4	98.0
0°-60°	645.8	99.9
0°-90°	646.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2079	2079	2079	2079	2079	
5°	2011	2010	2009	2013	2012	183
15°	1102	1089	1096	1093	1091	295
25°	259	269	292	262	254	124
35°	44	44	42	41	35	29
45°	12	14	14	14	12	8
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P778936

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9035-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2065.0	2063.5	2064.3	2065.4	2065.8
5°	2011.3	2009.5	2009.0	2013.2	2011.5
7.5°	1903.3	1900.5	1896.4	1905.9	1914.7
10°	1722.2	1719.2	1710.1	1714.6	1721.8
12.5°	1455.0	1445.0	1444.9	1459.1	1457.2
15°	1102.1	1088.8	1096.2	1092.6	1090.7
17.5°	741.2	736.1	745.9	742.9	730.1
20°	533.1	534.5	553.2	543.8	532.4
22.5°	389.0	393.8	416.0	391.8	382.9
25°	259.0	268.8	292.1	262.0	253.7
27.5°	159.3	163.8	187.4	157.3	152.8
30°	99.1	96.8	108.0	92.6	86.3
32.5°	65.0	62.2	65.7	59.0	53.9
35°	43.5	44.4	41.7	41.3	34.9
37.5°	27.2	31.2	27.6	29.4	22.5
40°	17.5	22.6	19.5	21.5	16.6
42.5°	14.4	17.5	16.0	17.0	14.7
45°	11.5	14.2	14.2	14.2	11.5
47.5°	6.3	9.5	12.1	9.7	6.8
50°	3.6	4.8	9.4	5.0	3.8
52.5°	2.5	2.8	6.4	2.9	2.6
55°	1.8	1.9	3.5	2.1	1.9
57.5°	1.4	1.5	1.8	1.5	1.4
60°	1.1	1.1	1.3	1.2	1.1
62.5°	0.8	0.8	0.9	0.8	0.8
65°	0.6	0.6	0.6	0.6	0.6
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)