

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778956

Luminaire Tested: LER4D05D010-EC4DR350210IC9030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778956
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR350210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 594.3 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778956

CATALOG NUMBER: LER4D05D010-EC4DR350210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P778956

CATALOG NUMBER: LER4D05D010-EC4DR350210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178685
5°	174487
10°	157255
15°	122051
20°	69229
25°	26932
30°	10043
35°	5509
40°	3609
45°	2194
50°	1394
55°	991
60°	721
65°	388
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2194 cd/sqm



TEST NUMBER: P778956

CATALOG NUMBER: LER4D05D010-EC4DR350210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.3	24.6
10°-20°	285.7	48.1
20°-30°	116.5	19.6
30°-40°	27.9	4.7
40°-50°	11.6	2.0
50°-60°	4.8	0.8
60°-70°	1.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.5	92.3
0°-40°	576.4	97.0
0°-60°	592.8	99.7
0°-90°	594.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1635	
5°	1591	146
15°	1079	286
25°	223	116
35°	41	28
45°	14	12
55°	5	5
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778956

CATALOG NUMBER: LER4D05D010-EC4DR350210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1635.4
2.5°	1625.6
5°	1590.9
7.5°	1521.6
10°	1417.4
12.5°	1270.6
15°	1079.0
17.5°	844.8
20°	595.4
22.5°	379.6
25°	223.4
27.5°	126.3
30°	79.6
32.5°	55.9
35°	41.3
37.5°	31.9
40°	25.3
42.5°	19.4
45°	14.2
47.5°	10.6
50°	8.2
52.5°	6.5
55°	5.2
57.5°	4.2
60°	3.3
62.5°	2.4
65°	1.5
67.5°	0.5
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)