

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780021

Luminaire Tested: LER4D15D010-EC4DR600215IC9040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D15D010-EC4DR600215IC9040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1537.8 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780021

CATALOG NUMBER: LER4D15D010-EC4DR600215IC9040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780021

CATALOG NUMBER: LER4D15D010-EC4DR600215IC9040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168152
5°	167742
10°	173309
15°	173485
20°	159631
25°	135770
30°	103454
35°	73160
40°	42960
45°	17337
50°	5779
55°	2781
60°	1136
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17337 cd/sqm



TEST NUMBER: P780021

CATALOG NUMBER: LER4D15D010-EC4DR600215IC9040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	9.6
10°-20°	424.9	27.6
20°-30°	508.5	33.1
30°-40°	340.1	22.1
40°-50°	100.8	6.6
50°-60°	14.5	0.9
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.0	70.3
0°-40°	1421.1	92.4
0°-60°	1536.5	99.9
0°-90°	1537.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1537.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1539	
5°	1529	148
15°	1534	425
25°	1126	509
35°	548	340
45°	112	101
55°	15	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780021

CATALOG NUMBER: LER4D15D010-EC4DR600215IC9040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1539.0
2.5°	1537.0
5°	1529.4
7.5°	1550.1
10°	1562.1
12.5°	1559.9
15°	1533.7
17.5°	1472.0
20°	1372.9
22.5°	1253.9
25°	1126.2
27.5°	982.4
30°	820.0
32.5°	675.1
35°	548.5
37.5°	421.7
40°	301.2
42.5°	198.6
45°	112.2
47.5°	57.4
50°	34.0
52.5°	22.1
55°	14.6
57.5°	9.4
60°	5.2
62.5°	2.2
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)