

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778997

Luminaire Tested: LER4D05D010-EC4DR450210IC9024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR450210IC9024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 597.6 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778997

CATALOG NUMBER: LER4D05D010-EC4DR450210IC9024-4LBS1H

Luminous Intensity Polar Plot



CATALOG NUMBER: LER4D05D010-EC4DR450210IC9024-4LBS1H

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95						
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81						
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77						
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73						
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69						
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66						
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63						
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60						

	0°
0°	115412
5°	112135
10°	107285
15°	98184
20°	77891
25°	48632
30°	26810
35°	12031
40°	4735
45°	2225
50°	1054
55°	552
60°	284
65°	52
70°	32
75°	0
80°	0
85°	0

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2225 cd/sqm



TEST NUMBER: P778997

CATALOG NUMBER: LER4D05D010-EC4DR450210IC9024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.1	16.1
10°-20°	236.4	39.6
20°-30°	187.2	31.3
30°-40°	62.3	10.4
40°-50°	12.3	2.1
50°-60°	2.8	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.7	87.0
0°-40°	582.0	97.4
0°-60°	597.2	99.9
0°-90°	597.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	1022	96
15°	868	236
25°	403	187
35°	90	62
45°	14	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778997

CATALOG NUMBER: LER4D05D010-EC4DR450210IC9024-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1056.3
2.5°	1049.5
5°	1022.4
7.5°	1000.0
10°	967.0
12.5°	922.9
15°	868.0
17.5°	785.4
20°	669.9
22.5°	532.3
25°	403.4
27.5°	295.4
30°	212.5
32.5°	144.5
35°	90.2
37.5°	53.5
40°	33.2
42.5°	21.8
45°	14.4
47.5°	9.3
50°	6.2
52.5°	4.2
55°	2.9
57.5°	1.9
60°	1.3
62.5°	0.7
65°	0.2
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)