

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780033

Luminaire Tested: LER4D15D010-EC4DR650215IC9027-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D15D010-EC4DR650215IC9027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1199.6 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780033

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780033

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63613
5°	63452
10°	63397
15°	61444
20°	55937
25°	48744
30°	40538
35°	32127
40°	23185
45°	14644
50°	7641
55°	4063
60°	2126
65°	1175
70°	495
75°	542
80°	370
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14644 cd/sqm



TEST NUMBER: P780033

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	8.6
10°-20°	282.1	23.5
20°-30°	344.8	28.7
30°-40°	279.7	23.3
40°-50°	139.4	11.6
50°-60°	38.9	3.2
60°-70°	8.8	0.7
70°-80°	2.3	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.8	60.8
0°-40°	1009.6	84.2
0°-60°	1187.8	99.0
0°-90°	1199.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1089	
5°	1082	103
15°	1016	282
25°	756	345
35°	451	280
45°	177	139
55°	40	39
65°	8	9
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P780033

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1089.2
2.5°	1088.4
5°	1082.3
7.5°	1078.8
10°	1069.0
12.5°	1049.1
15°	1016.2
17.5°	964.6
20°	900.0
22.5°	830.2
25°	756.4
27.5°	677.5
30°	601.1
32.5°	525.8
35°	450.6
37.5°	375.5
40°	304.1
42.5°	237.2
45°	177.3
47.5°	123.6
50°	84.1
52.5°	57.9
55°	39.9
57.5°	26.9
60°	18.2
62.5°	12.7
65°	8.5
67.5°	4.3
70°	2.9
72.5°	2.7
75°	2.4
77.5°	1.6
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)