

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779099

Luminaire Tested: LER4D05D010-EC4DR650210IC9027-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR650210IC9027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 539.3 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779099

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P779099

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28600
5°	28528
10°	28502
15°	27626
20°	25153
25°	21917
30°	18229
35°	14445
40°	10422
45°	6591
50°	3435
55°	1823
60°	958
65°	525
70°	222
75°	248
80°	168
85°	134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6591 cd/sqm



TEST NUMBER: P779099

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	8.6
10°-20°	126.8	23.5
20°-30°	155.0	28.7
30°-40°	125.8	23.3
40°-50°	62.7	11.6
50°-60°	17.5	3.2
60°-70°	4.0	0.7
70°-80°	1.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.1	60.8
0°-40°	453.9	84.2
0°-60°	534.1	99.0
0°-90°	539.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	487	46
15°	457	127
25°	340	155
35°	203	126
45°	80	63
55°	18	17
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P779099

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	489.7
2.5°	489.4
5°	486.6
7.5°	485.0
10°	480.6
12.5°	471.7
15°	456.9
17.5°	433.7
20°	404.7
22.5°	373.3
25°	340.1
27.5°	304.6
30°	270.3
32.5°	236.4
35°	202.6
37.5°	168.8
40°	136.7
42.5°	106.6
45°	79.8
47.5°	55.6
50°	37.8
52.5°	26.1
55°	17.9
57.5°	12.1
60°	8.2
62.5°	5.7
65°	3.8
67.5°	1.9
70°	1.3
72.5°	1.2
75°	1.1
77.5°	0.7
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)