

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780042

Luminaire Tested: LER4D15D010-EC4DR650215IC9035-4LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P780042  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D15D010-EC4DR650215IC9035-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1373.0 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P780042

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9035-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P780042

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9035-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 113 | 110 | 107 | 105 |  | 111 | 108 | 105 | 103 |  | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 95  | 94  |
| 2   | 107 | 102 | 97  | 94  |  | 105 | 100 | 96  | 92  |  | 97  | 93  | 90  |  | 94  | 91  | 88  |  | 91  | 89  | 87  |
| 3   | 101 | 94  | 88  | 84  |  | 99  | 92  | 87  | 83  |  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  | 82  | 80  |
| 4   | 95  | 87  | 81  | 76  |  | 93  | 86  | 80  | 76  |  | 84  | 79  | 75  |  | 82  | 77  | 74  |  | 80  | 76  | 73  |
| 5   | 90  | 81  | 74  | 70  |  | 88  | 80  | 74  | 69  |  | 78  | 73  | 69  |  | 76  | 72  | 68  |  | 75  | 71  | 68  |
| 6   | 85  | 75  | 69  | 64  |  | 83  | 74  | 68  | 64  |  | 73  | 67  | 63  |  | 71  | 67  | 63  |  | 70  | 66  | 62  |
| 7   | 80  | 70  | 64  | 59  |  | 79  | 69  | 63  | 59  |  | 68  | 63  | 59  |  | 67  | 62  | 58  |  | 66  | 61  | 58  |
| 8   | 76  | 66  | 59  | 55  |  | 75  | 65  | 59  | 55  |  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  | 57  | 54  |
| 9   | 72  | 61  | 55  | 51  |  | 71  | 61  | 55  | 51  |  | 60  | 54  | 51  |  | 59  | 54  | 50  |  | 58  | 54  | 50  |
| 10  | 68  | 58  | 52  | 47  |  | 67  | 57  | 51  | 47  |  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 55  | 50  | 47  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 72806 |
| 5°  | 72621 |
| 10° | 72559 |
| 15° | 70326 |
| 20° | 64023 |
| 25° | 55787 |
| 30° | 46405 |
| 35° | 36768 |
| 40° | 26539 |
| 45° | 16767 |
| 50° | 8741  |
| 55° | 4643  |
| 60° | 2441  |
| 65° | 1340  |
| 70° | 564   |
| 75° | 632   |
| 80° | 437   |
| 85° | 402   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16767 cd/sqm



TEST NUMBER: P780042

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9035-4LBS1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 117.9  | 8.6       |
| 10°-20°   | 322.8  | 23.5      |
| 20°-30°   | 394.6  | 28.7      |
| 30°-40°   | 320.2  | 23.3      |
| 40°-50°   | 159.6  | 11.6      |
| 50°-60°   | 44.5   | 3.2       |
| 60°-70°   | 10.1   | 0.7       |
| 70°-80°   | 2.6    | 0.2       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 835.3  | 60.8      |
| 0°-40°    | 1155.5 | 84.2      |
| 0°-60°    | 1359.6 | 99.0      |
| 0°-90°    | 1373.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1373.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1247 |      |
| 5°  | 1239 | 118  |
| 15° | 1163 | 323  |
| 25° | 866  | 395  |
| 35° | 516  | 320  |
| 45° | 203  | 160  |
| 55° | 46   | 45   |
| 65° | 10   | 10   |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P780042

CATALOG NUMBER: LER4D15D010-EC4DR650215IC9035-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1246.6 |
| 2.5°  | 1245.7 |
| 5°    | 1238.7 |
| 7.5°  | 1234.7 |
| 10°   | 1223.5 |
| 12.5° | 1200.8 |
| 15°   | 1163.1 |
| 17.5° | 1104.1 |
| 20°   | 1030.1 |
| 22.5° | 950.2  |
| 25°   | 865.7  |
| 27.5° | 775.4  |
| 30°   | 688.1  |
| 32.5° | 601.8  |
| 35°   | 515.7  |
| 37.5° | 429.8  |
| 40°   | 348.1  |
| 42.5° | 271.5  |
| 45°   | 203.0  |
| 47.5° | 141.4  |
| 50°   | 96.2   |
| 52.5° | 66.3   |
| 55°   | 45.6   |
| 57.5° | 30.8   |
| 60°   | 20.9   |
| 62.5° | 14.5   |
| 65°   | 9.7    |
| 67.5° | 4.9    |
| 70°   | 3.3    |
| 72.5° | 3.1    |
| 75°   | 2.8    |
| 77.5° | 1.8    |
| 80°   | 1.3    |
| 82.5° | 0.9    |
| 85°   | 0.6    |
| 87.5° | 0.3    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report





— 0°-180°







(END OF REPORT)