

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779237

Luminaire Tested: LER4D08D010-EC4DR300210IC9024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR300210IC9024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 670.4 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779237

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9024-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P779237

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	164997	164997	164997
5°	160264	160072	160272
10°	138808	137828	138777
15°	90567	90076	89632
20°	45037	46723	44980
25°	22685	25582	22220
30°	9086	9899	7919
35°	4214	4037	3383
40°	1819	2018	1709
45°	1288	1591	1299
50°	441	1155	464
55°	254	480	267
60°	168	214	168
65°	109	109	109
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1591 cd/sqm



TEST NUMBER: P779237

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.6	28.3
10°-20°	305.3	45.5
20°-30°	131.9	19.7
30°-40°	30.1	4.5
40°-50°	10.3	1.5
50°-60°	2.5	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.8	93.5
0°-40°	656.8	98.0
0°-60°	669.7	99.9
0°-90°	670.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2156	2156	2156	2156	2156	
5°	2086	2084	2083	2088	2086	190
15°	1143	1129	1137	1133	1131	306
25°	269	279	303	272	263	129
35°	45	46	43	43	36	31
45°	12	15	15	15	12	8
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P779237

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2155.6	2155.6	2155.6	2155.6	2155.6
2.5°	2141.3	2139.9	2140.7	2141.7	2142.1
5°	2085.8	2083.8	2083.3	2087.7	2085.9
7.5°	1973.7	1970.8	1966.5	1976.3	1985.6
10°	1785.9	1782.7	1773.3	1778.0	1785.5
12.5°	1508.8	1498.5	1498.3	1513.1	1511.1
15°	1142.9	1129.1	1136.7	1133.1	1131.1
17.5°	768.6	763.3	773.4	770.4	757.2
20°	552.9	554.3	573.6	563.9	552.2
22.5°	403.4	408.4	431.4	406.3	397.1
25°	268.6	278.7	302.9	271.7	263.1
27.5°	165.2	169.9	194.3	163.1	158.4
30°	102.8	100.4	112.0	96.1	89.6
32.5°	67.4	64.5	68.2	61.2	55.9
35°	45.1	46.1	43.2	42.9	36.2
37.5°	28.1	32.4	28.6	30.5	23.3
40°	18.2	23.5	20.2	22.3	17.1
42.5°	14.9	18.1	16.6	17.6	15.2
45°	11.9	14.7	14.7	14.7	12.0
47.5°	6.6	9.9	12.6	10.0	7.0
50°	3.7	5.0	9.7	5.2	3.9
52.5°	2.5	2.9	6.6	3.0	2.6
55°	1.9	2.0	3.6	2.1	2.0
57.5°	1.5	1.6	1.9	1.6	1.5
60°	1.1	1.1	1.4	1.3	1.1
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.6	0.6	0.6	0.6	0.6
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)