

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779340

Luminaire Tested: LER4D08D010-EC4DR500210IC9030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR500210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 772.4 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779340

CATALOG NUMBER: LER4D08D010-EC4DR500210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P779340

CATALOG NUMBER: LER4D08D010-EC4DR500210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135975
5°	134553
10°	132337
15°	120501
20°	100262
25°	71176
30°	37672
35°	15352
40°	5705
45°	2611
50°	1071
55°	552
60°	284
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2611 cd/sqm



TEST NUMBER: P779340

CATALOG NUMBER: LER4D08D010-EC4DR500210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	15.0
10°-20°	293.0	37.9
20°-30°	263.2	34.1
30°-40°	82.4	10.7
40°-50°	14.4	1.9
50°-60°	2.9	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	672.2	87.0
0°-40°	754.6	97.7
0°-60°	771.9	99.9
0°-90°	772.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1244	
5°	1227	116
15°	1065	293
25°	590	263
35°	115	82
45°	17	14
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779340

CATALOG NUMBER: LER4D08D010-EC4DR500210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1244.5
2.5°	1238.3
5°	1226.8
7.5°	1209.2
10°	1192.8
12.5°	1140.3
15°	1065.3
17.5°	970.0
20°	862.3
22.5°	737.8
25°	590.4
27.5°	434.1
30°	298.6
32.5°	194.4
35°	115.1
37.5°	66.1
40°	40.0
42.5°	26.0
45°	16.9
47.5°	10.3
50°	6.3
52.5°	4.3
55°	2.9
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)