

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780197

Luminaire Tested: LER4D20D010-EC4DR3520359024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR3520359024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1617.4 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780197

CATALOG NUMBER: LER4D20D010-EC4DR3520359024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780197

CATALOG NUMBER: LER4D20D010-EC4DR3520359024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	94	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	486265
5°	474829
10°	427953
15°	332162
20°	188397
25°	73298
30°	27340
35°	14992
40°	9799
45°	5964
50°	3791
55°	2686
60°	1967
65°	1060
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5964 cd/sqm



TEST NUMBER: P780197

CATALOG NUMBER: LER4D20D010-EC4DR3520359024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	398.2	24.6
10°-20°	777.4	48.1
20°-30°	317.1	19.6
30°-40°	75.9	4.7
40°-50°	31.6	2.0
50°-60°	13.1	0.8
60°-70°	4.1	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1492.6	92.3
0°-40°	1568.5	97.0
0°-60°	1613.2	99.7
0°-90°	1617.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1617.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4450	
5°	4329	398
15°	2936	777
25°	608	317
35°	112	76
45°	39	32
55°	14	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780197

CATALOG NUMBER: LER4D20D010-EC4DR3520359024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4450.5
2.5°	4423.8
5°	4329.3
7.5°	4141.0
10°	3857.3
12.5°	3457.8
15°	2936.5
17.5°	2298.9
20°	1620.3
22.5°	1033.2
25°	608.0
27.5°	343.7
30°	216.7
32.5°	152.2
35°	112.4
37.5°	86.9
40°	68.7
42.5°	52.9
45°	38.6
47.5°	28.9
50°	22.3
52.5°	17.7
55°	14.1
57.5°	11.4
60°	9.0
62.5°	6.5
65°	4.1
67.5°	1.4
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)