

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779420

Luminaire Tested: LER4D08D010-EC4DR650210IC9040-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR650210IC9040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 694.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779420

CATALOG NUMBER: LER4D08D010-EC4DR650210IC9040-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P779420

CATALOG NUMBER: LER4D08D010-EC4DR650210IC9040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36829
5°	36736
10°	36704
15°	35571
20°	32381
25°	28225
30°	23476
35°	18602
40°	13426
45°	8483
50°	4416
55°	2352
60°	1226
65°	677
70°	290
75°	316
80°	202
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8483 cd/sqm



TEST NUMBER: P779420

CATALOG NUMBER: LER4D08D010-EC4DR650210IC9040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	8.6
10°-20°	163.3	23.5
20°-30°	199.6	28.7
30°-40°	162.0	23.3
40°-50°	80.7	11.6
50°-60°	22.5	3.2
60°-70°	5.1	0.7
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.5	60.8
0°-40°	584.5	84.2
0°-60°	687.7	99.0
0°-90°	694.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	631	
5°	627	60
15°	588	163
25°	438	200
35°	261	162
45°	103	81
55°	23	23
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P779420

CATALOG NUMBER: LER4D08D010-EC4DR650210IC9040-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	630.6
2.5°	630.1
5°	626.6
7.5°	624.6
10°	618.9
12.5°	607.4
15°	588.3
17.5°	558.5
20°	521.0
22.5°	480.6
25°	438.0
27.5°	392.2
30°	348.1
32.5°	304.4
35°	260.9
37.5°	217.4
40°	176.1
42.5°	137.3
45°	102.7
47.5°	71.6
50°	48.6
52.5°	33.5
55°	23.1
57.5°	15.6
60°	10.5
62.5°	7.3
65°	4.9
67.5°	2.5
70°	1.7
72.5°	1.5
75°	1.4
77.5°	0.9
80°	0.6
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)