

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779430

Luminaire Tested: LER4D08D010-EC4DR700210IC9024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR700210IC9024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 727.6 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779430

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P779430

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105	111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94	105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84	99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	76	93	86	80	76		83	78	75		81	77	74		79	76	73
5	89	80	74	69	88	79	73	69		78	72	68		76	71	68		74	70	67
6	84	75	68	63	83	74	68	63		72	67	63		71	66	62		69	65	62
7	80	69	63	58	78	69	62	58		67	62	58		66	61	57		65	61	57
8	75	65	58	54	74	64	58	54		63	57	53		62	57	53		61	56	53
9	71	61	54	50	70	60	54	50		59	53	50		58	53	49		57	53	49
10	67	57	50	46	66	56	50	46		55	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62748
5°	62593
10°	62452
15°	62440
20°	61834
25°	58072
30°	51777
35°	41282
40°	27413
45°	16394
50°	8499
55°	4457
60°	1573
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16394 cd/sqm



TEST NUMBER: P779430

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	7.5
10°-20°	155.7	21.4
20°-30°	219.6	30.2
30°-40°	189.5	26.1
40°-50°	84.9	11.7
50°-60°	22.2	3.1
60°-70°	1.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.5	59.0
0°-40°	619.1	85.1
0°-60°	726.2	99.8
0°-90°	727.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	571	54
15°	552	156
25°	482	220
35°	310	190
45°	106	85
55°	23	22
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779430

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.3
2.5°	573.7
5°	570.7
7.5°	568.2
10°	562.9
12.5°	558.2
15°	552.0
17.5°	544.9
20°	531.8
22.5°	510.2
25°	481.7
27.5°	448.8
30°	410.4
32.5°	363.4
35°	309.5
37.5°	250.0
40°	192.2
42.5°	146.0
45°	106.1
47.5°	73.1
50°	50.0
52.5°	34.5
55°	23.4
57.5°	14.2
60°	7.2
62.5°	2.3
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)