

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779437

Luminaire Tested: LER4D08D010-EC4DR700210IC9030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR700210IC9030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 794.3 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779437

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P779437

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68496
5°	68329
10°	68176
15°	68163
20°	67496
25°	63400
30°	56521
35°	45070
40°	29924
45°	17893
50°	9264
55°	4877
60°	1726
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17893 cd/sqm



TEST NUMBER: P779437

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	7.5
10°-20°	169.9	21.4
20°-30°	239.7	30.2
30°-40°	206.9	26.1
40°-50°	92.7	11.7
50°-60°	24.3	3.1
60°-70°	1.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.9	59.0
0°-40°	675.8	85.1
0°-60°	792.7	99.8
0°-90°	794.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	794.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	627	
5°	623	59
15°	603	170
25°	526	240
35°	338	207
45°	116	93
55°	26	24
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779437

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	626.9
2.5°	626.2
5°	623.0
7.5°	620.3
10°	614.5
12.5°	609.3
15°	602.6
17.5°	594.8
20°	580.5
22.5°	556.9
25°	525.9
27.5°	489.9
30°	448.0
32.5°	396.7
35°	337.9
37.5°	273.0
40°	209.8
42.5°	159.4
45°	115.8
47.5°	79.8
50°	54.5
52.5°	37.6
55°	25.6
57.5°	15.5
60°	7.9
62.5°	2.5
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)