

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780201

Luminaire Tested: LER4D20D010-EC4DR3520359027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR3520359027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1795.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780201

CATALOG NUMBER: LER4D20D010-EC4DR3520359027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780201

CATALOG NUMBER: LER4D20D010-EC4DR3520359027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96			
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75			
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70			
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	539781
5°	527102
10°	475061
15°	368721
20°	209140
25°	81363
30°	30355
35°	16633
40°	10883
45°	6629
50°	4215
55°	2972
60°	2185
65°	1189
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6629 cd/sqm



TEST NUMBER: P780201

CATALOG NUMBER: LER4D20D010-EC4DR3520359027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	442.0	24.6
10°-20°	863.0	48.1
20°-30°	352.0	19.6
30°-40°	84.2	4.7
40°-50°	35.1	2.0
50°-60°	14.5	0.8
60°-70°	4.6	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.9	92.3
0°-40°	1741.1	97.0
0°-60°	1790.8	99.7
0°-90°	1795.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1795.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4940	
5°	4806	442
15°	3260	863
25°	675	352
35°	125	84
45°	43	35
55°	16	15
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780201

CATALOG NUMBER: LER4D20D010-EC4DR3520359027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4940.3
2.5°	4910.7
5°	4805.9
7.5°	4596.8
10°	4281.9
12.5°	3838.4
15°	3259.7
17.5°	2551.9
20°	1798.7
22.5°	1146.9
25°	674.9
27.5°	381.5
30°	240.6
32.5°	168.9
35°	124.7
37.5°	96.4
40°	76.3
42.5°	58.7
45°	42.9
47.5°	32.1
50°	24.8
52.5°	19.7
55°	15.6
57.5°	12.7
60°	10.0
62.5°	7.3
65°	4.6
67.5°	1.6
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)