

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780233

Luminaire Tested: LER4D20D010-EC4DR4020359035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR4020359035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2139.1 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780233

CATALOG NUMBER: LER4D20D010-EC4DR4020359035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780233

CATALOG NUMBER: LER4D20D010-EC4DR4020359035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544162
5°	541514
10°	511851
15°	435131
20°	296577
25°	123739
30°	38909
35°	18087
40°	9998
45°	4589
50°	2227
55°	1219
60°	634
65°	233
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4589 cd/sqm



TEST NUMBER: P780233

CATALOG NUMBER: LER4D20D010-EC4DR4020359035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	461.0	21.6
10°-20°	1032.8	48.3
20°-30°	517.0	24.2
30°-40°	94.8	4.4
40°-50°	26.1	1.2
50°-60°	6.1	0.3
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2010.8	94.0
0°-40°	2105.6	98.4
0°-60°	2137.9	99.9
0°-90°	2139.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2139.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4980	
5°	4937	461
15°	3847	1033
25°	1026	517
35°	136	95
45°	30	26
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780233

CATALOG NUMBER: LER4D20D010-EC4DR4020359035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4980.4
2.5°	4973.1
5°	4937.3
7.5°	4823.3
10°	4613.5
12.5°	4286.5
15°	3846.8
17.5°	3275.2
20°	2550.7
22.5°	1739.0
25°	1026.4
27.5°	542.6
30°	308.4
32.5°	199.3
35°	135.6
37.5°	96.9
40°	70.1
42.5°	48.0
45°	29.7
47.5°	18.9
50°	13.1
52.5°	9.3
55°	6.4
57.5°	4.1
60°	2.9
62.5°	1.7
65°	0.9
67.5°	0.6
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)