

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779609

Luminaire Tested: LER4D10D010-EC4DR400210IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR400210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1159.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779609

CATALOG NUMBER: LER4D10D010-EC4DR400210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P779609

CATALOG NUMBER: LER4D10D010-EC4DR400210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	112	110	108	112	110	108	107		106	105	103			103	101	100			96
2	110	106	103	100	108	105	102	99		102	99	97			99	97	95			92
3	106	101	97	94	104	100	96	93		97	94	92			95	93	90			88
4	102	97	92	89	101	95	91	88		93	90	87			92	89	86			84
5	99	92	88	84	97	91	87	84		90	86	83			88	85	83			81
6	95	88	84	80	94	88	83	80		86	82	80			85	82	79			77
7	92	85	80	77	91	84	80	77		83	79	76			82	79	76			74
8	89	82	77	74	88	81	77	74		80	76	73			79	76	73			72
9	86	79	74	71	85	78	74	71		77	73	71			76	73	70			69
10	83	76	71	68	82	75	71	68		75	71	68			74	70	68			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294917
5°	293488
10°	277410
15°	235834
20°	160736
25°	67065
30°	21082
35°	9804
40°	5420
45°	2488
50°	1207
55°	667
60°	350
65°	129
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2488 cd/sqm

TEST NUMBER: P779609

CATALOG NUMBER: LER4D10D010-EC4DR400210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.9	21.6
10°-20°	559.7	48.3
20°-30°	280.2	24.2
30°-40°	51.4	4.4
40°-50°	14.2	1.2
50°-60°	3.3	0.3
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1089.8	94.0
0°-40°	1141.2	98.4
0°-60°	1158.7	99.9
0°-90°	1159.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2699	
5°	2676	250
15°	2085	560
25°	556	280
35°	74	51
45°	16	14
55°	4	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779609

CATALOG NUMBER: LER4D10D010-EC4DR400210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2699.2
2.5°	2695.3
5°	2675.9
7.5°	2614.0
10°	2500.4
12.5°	2323.1
15°	2084.9
17.5°	1775.0
20°	1382.4
22.5°	942.4
25°	556.3
27.5°	294.1
30°	167.1
32.5°	108.0
35°	73.5
37.5°	52.5
40°	38.0
42.5°	26.0
45°	16.1
47.5°	10.3
50°	7.1
52.5°	5.0
55°	3.5
57.5°	2.2
60°	1.6
62.5°	1.0
65°	0.5
67.5°	0.3
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)