

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779628

Luminaire Tested: LER4D10D010-EC4DR450210IC9030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR450210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1009.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779628

CATALOG NUMBER: LER4D10D010-EC4DR450210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P779628

CATALOG NUMBER: LER4D10D010-EC4DR450210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95						
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81						
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77						
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73						
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69						
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66						
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63						
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194867
5°	189315
10°	181120
15°	165759
20°	131516
25°	82099
30°	45255
35°	20314
40°	8002
45°	3770
50°	1785
55°	933
60°	459
65°	103
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3770 cd/sqm



TEST NUMBER: P779628

CATALOG NUMBER: LER4D10D010-EC4DR450210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.2	16.1
10°-20°	399.1	39.6
20°-30°	316.1	31.3
30°-40°	105.3	10.4
40°-50°	20.9	2.1
50°-60°	4.7	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.4	87.0
0°-40°	982.7	97.4
0°-60°	1008.3	99.9
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1784	
5°	1726	162
15°	1465	399
25°	681	316
35°	152	105
45°	24	21
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779628

CATALOG NUMBER: LER4D10D010-EC4DR450210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1783.5
2.5°	1771.8
5°	1726.1
7.5°	1688.4
10°	1632.5
12.5°	1558.2
15°	1465.4
17.5°	1326.0
20°	1131.1
22.5°	898.7
25°	681.0
27.5°	498.7
30°	358.7
32.5°	244.0
35°	152.3
37.5°	90.4
40°	56.1
42.5°	36.9
45°	24.4
47.5°	15.7
50°	10.5
52.5°	7.0
55°	4.9
57.5°	3.2
60°	2.1
62.5°	1.1
65°	0.4
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)