

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780278

Luminaire Tested: LER4D20D010-EC4DR5020359030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR5020359030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2114.1 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780278

CATALOG NUMBER: LER4D20D010-EC4DR5020359030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P780278

CATALOG NUMBER: LER4D20D010-EC4DR5020359030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	74	74	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	63	63	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	372197
5°	368299
10°	362229
15°	329844
20°	274462
25°	194830
30°	103126
35°	42029
40°	15604
45°	7139
50°	2924
55°	1524
60°	743
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7139 cd/sqm



TEST NUMBER: P780278

CATALOG NUMBER: LER4D20D010-EC4DR5020359030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.4	15.0
10°-20°	802.1	37.9
20°-30°	720.5	34.1
30°-40°	225.6	10.7
40°-50°	39.5	1.9
50°-60°	7.8	0.4
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1840.0	87.0
0°-40°	2065.6	97.7
0°-60°	2113.0	99.9
0°-90°	2114.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2114.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3406	
5°	3358	317
15°	2916	802
25°	1616	721
35°	315	226
45°	46	39
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780278

CATALOG NUMBER: LER4D20D010-EC4DR5020359030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3406.5
2.5°	3389.6
5°	3358.0
7.5°	3309.7
10°	3264.9
12.5°	3121.3
15°	2916.0
17.5°	2655.2
20°	2360.5
22.5°	2019.6
25°	1616.1
27.5°	1188.1
30°	817.4
32.5°	532.2
35°	315.1
37.5°	180.9
40°	109.4
42.5°	71.2
45°	46.2
47.5°	28.1
50°	17.2
52.5°	11.8
55°	8.0
57.5°	5.4
60°	3.4
62.5°	2.0
65°	0.9
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)