

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779701

Luminaire Tested: LER4D10D010-EC4DR600210IC9030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR600210IC9030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1054.9 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779701

CATALOG NUMBER: LER4D10D010-EC4DR600210IC9030-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P779701

CATALOG NUMBER: LER4D10D010-EC4DR600210IC9030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115347
5°	115063
10°	118890
15°	119008
20°	109506
25°	93141
30°	70967
35°	50192
40°	29467
45°	11882
50°	3978
55°	1905
60°	787
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11882 cd/sqm



TEST NUMBER: P779701

CATALOG NUMBER: LER4D10D010-EC4DR600210IC9030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	9.6
10°-20°	291.5	27.6
20°-30°	348.9	33.1
30°-40°	233.3	22.1
40°-50°	69.2	6.6
50°-60°	9.9	0.9
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	741.5	70.3
0°-40°	974.9	92.4
0°-60°	1054.0	99.9
0°-90°	1054.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	1049	101
15°	1052	291
25°	773	349
35°	376	233
45°	77	69
55°	10	10
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779701

CATALOG NUMBER: LER4D10D010-EC4DR600210IC9030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1055.7
2.5°	1054.3
5°	1049.1
7.5°	1063.3
10°	1071.6
12.5°	1070.1
15°	1052.1
17.5°	1009.8
20°	941.8
22.5°	860.2
25°	772.6
27.5°	673.9
30°	562.5
32.5°	463.1
35°	376.3
37.5°	289.3
40°	206.6
42.5°	136.2
45°	76.9
47.5°	39.4
50°	23.4
52.5°	15.1
55°	10.0
57.5°	6.4
60°	3.6
62.5°	1.5
65°	0.5
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)