

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780319

Luminaire Tested: LER4D20D010-EC4DR6020359024-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6020359024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1613.9 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780319

CATALOG NUMBER: LER4D20D010-EC4DR6020359024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P780319

CATALOG NUMBER: LER4D20D010-EC4DR6020359024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176467
5°	176033
10°	181885
15°	182070
20°	167514
25°	142485
30°	108576
35°	76775
40°	45085
45°	18187
50°	6085
55°	2934
60°	1202
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18187 cd/sqm



TEST NUMBER: P780319

CATALOG NUMBER: LER4D20D010-EC4DR6020359024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.8	9.6
10°-20°	445.9	27.6
20°-30°	533.7	33.1
30°-40°	357.0	22.1
40°-50°	105.8	6.6
50°-60°	15.2	0.9
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1134.4	70.3
0°-40°	1491.4	92.4
0°-60°	1612.5	99.9
0°-90°	1613.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1613.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1615	
5°	1605	155
15°	1610	446
25°	1182	534
35°	576	357
45°	118	106
55°	15	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780319

CATALOG NUMBER: LER4D20D010-EC4DR6020359024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1615.1
2.5°	1613.0
5°	1605.0
7.5°	1626.8
10°	1639.4
12.5°	1637.1
15°	1609.6
17.5°	1544.7
20°	1440.7
22.5°	1316.0
25°	1181.9
27.5°	1031.0
30°	860.6
32.5°	708.5
35°	575.6
37.5°	442.5
40°	316.1
42.5°	208.4
45°	117.7
47.5°	60.2
50°	35.8
52.5°	23.1
55°	15.4
57.5°	9.9
60°	5.5
62.5°	2.3
65°	0.7
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)