

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779901

Luminaire Tested: LER4D15D010-EC4DR350215IC9040-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P779901  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D15D010-EC4DR350215IC9040-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1464.7 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P779901

CATALOG NUMBER: LER4D15D010-EC4DR350215IC9040-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P779901

CATALOG NUMBER: LER4D15D010-EC4DR350215IC9040-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99  | 98  | 98  | 96  |    |    |
| 2   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 99  | 102 | 99  | 97  | 99  | 97  | 95  | 96  | 95  | 93  | 92  |    |    |
| 3   | 106 | 101 | 97  | 94  | 105 | 100 | 96  | 94  | 97  | 95  | 92  | 95  | 93  | 91  | 93  | 91  | 89  | 88  |    |    |
| 4   | 103 | 97  | 92  | 89  | 101 | 96  | 92  | 89  | 94  | 90  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 84  |    |    |
| 5   | 99  | 93  | 88  | 85  | 98  | 92  | 87  | 84  | 90  | 86  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 81  |    |    |
| 6   | 96  | 89  | 84  | 81  | 94  | 88  | 84  | 81  | 87  | 83  | 80  | 85  | 82  | 80  | 84  | 81  | 79  | 78  |    |    |
| 7   | 93  | 85  | 81  | 78  | 91  | 85  | 80  | 77  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 76  | 75  |    |    |
| 8   | 90  | 82  | 78  | 74  | 88  | 82  | 77  | 74  | 81  | 77  | 74  | 80  | 76  | 74  | 79  | 76  | 73  | 72  |    |    |
| 9   | 87  | 79  | 75  | 72  | 86  | 79  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 77  | 73  | 71  | 70  |    |    |
| 10  | 84  | 77  | 72  | 69  | 83  | 76  | 72  | 69  | 76  | 72  | 69  | 75  | 71  | 69  | 74  | 71  | 69  | 68  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 440343 |
| 5°  | 429993 |
| 10° | 387546 |
| 15° | 300796 |
| 20° | 170607 |
| 25° | 66366  |
| 30° | 24766  |
| 35° | 13578  |
| 40° | 8872   |
| 45° | 5393   |
| 50° | 3434   |
| 55° | 2419   |
| 60° | 1770   |
| 65° | 957    |
| 70° | 64     |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5393 cd/sqm



TEST NUMBER: P779901

CATALOG NUMBER: LER4D15D010-EC4DR350215IC9040-4LBS1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 360.6  | 24.6      |
| 10°-20°   | 704.0  | 48.1      |
| 20°-30°   | 287.1  | 19.6      |
| 30°-40°   | 68.7   | 4.7       |
| 40°-50°   | 28.6   | 2.0       |
| 50°-60°   | 11.8   | 0.8       |
| 60°-70°   | 3.7    | 0.3       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1351.7 | 92.3      |
| 0°-40°    | 1420.4 | 97.0      |
| 0°-60°    | 1460.8 | 99.7      |
| 0°-90°    | 1464.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1464.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4030 |      |
| 5°  | 3920 | 361  |
| 15° | 2659 | 704  |
| 25° | 550  | 287  |
| 35° | 102  | 69   |
| 45° | 35   | 29   |
| 55° | 13   | 12   |
| 65° | 4    | 4    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P779901

CATALOG NUMBER: LER4D15D010-EC4DR350215IC9040-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4030.2 |
| 2.5°  | 4006.0 |
| 5°    | 3920.5 |
| 7.5°  | 3750.0 |
| 10°   | 3493.1 |
| 12.5° | 3131.3 |
| 15°   | 2659.2 |
| 17.5° | 2081.8 |
| 20°   | 1467.3 |
| 22.5° | 935.6  |
| 25°   | 550.5  |
| 27.5° | 311.2  |
| 30°   | 196.3  |
| 32.5° | 137.8  |
| 35°   | 101.8  |
| 37.5° | 78.7   |
| 40°   | 62.2   |
| 42.5° | 47.9   |
| 45°   | 34.9   |
| 47.5° | 26.1   |
| 50°   | 20.2   |
| 52.5° | 16.0   |
| 55°   | 12.7   |
| 57.5° | 10.3   |
| 60°   | 8.1    |
| 62.5° | 6.0    |
| 65°   | 3.7    |
| 67.5° | 1.3    |
| 70°   | 0.2    |
| 72.5° | 0.2    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.2    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)