

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779962

Luminaire Tested: LER4D15D010-EC4DR500215IC9027-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D15D010-EC4DR500215IC9027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1491.1 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779962

CATALOG NUMBER: LER4D15D010-EC4DR500215IC9027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P779962

CATALOG NUMBER: LER4D15D010-EC4DR500215IC9027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262510
5°	259751
10°	255476
15°	232632
20°	193571
25°	137410
30°	72733
35°	29638
40°	11011
45°	5037
50°	2057
55°	1086
60°	524
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5037 cd/sqm

TEST NUMBER: P779962

CATALOG NUMBER: LER4D15D010-EC4DR500215IC9027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.9	15.0
10°-20°	565.7	37.9
20°-30°	508.2	34.1
30°-40°	159.1	10.7
40°-50°	27.8	1.9
50°-60°	5.5	0.4
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.8	87.0
0°-40°	1456.9	97.7
0°-60°	1490.2	99.9
0°-90°	1491.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1491.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2403	
5°	2368	224
15°	2057	566
25°	1140	508
35°	222	159
45°	33	28
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779962

CATALOG NUMBER: LER4D15D010-EC4DR500215IC9027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2402.6
2.5°	2390.6
5°	2368.3
7.5°	2334.3
10°	2302.7
12.5°	2201.4
15°	2056.6
17.5°	1872.7
20°	1664.8
22.5°	1424.4
25°	1139.8
27.5°	838.0
30°	576.5
32.5°	375.3
35°	222.2
37.5°	127.6
40°	77.2
42.5°	50.2
45°	32.6
47.5°	19.8
50°	12.1
52.5°	8.3
55°	5.7
57.5°	3.8
60°	2.4
62.5°	1.4
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)