

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779998

Luminaire Tested: LER4D15D010-EC4DR550215IC9040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D15D010-EC4DR550215IC9040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1646.5 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779998

CATALOG NUMBER: LER4D15D010-EC4DR550215IC9040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P779998

CATALOG NUMBER: LER4D15D010-EC4DR550215IC9040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201728
5°	193713
10°	192991
15°	187443
20°	168061
25°	138892
30°	104918
35°	76082
40°	48694
45°	22235
50°	7275
55°	3143
60°	1355
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22235 cd/sqm



TEST NUMBER: P779998

CATALOG NUMBER: LER4D15D010-EC4DR550215IC9040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	10.2
10°-20°	458.7	27.9
20°-30°	522.7	31.7
30°-40°	355.9	21.6
40°-50°	122.6	7.4
50°-60°	17.0	1.0
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.4	69.8
0°-40°	1505.3	91.4
0°-60°	1644.9	99.9
0°-90°	1646.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1646.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1846	
5°	1766	168
15°	1657	459
25°	1152	523
35°	570	356
45°	144	123
55°	16	17
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779998

CATALOG NUMBER: LER4D15D010-EC4DR550215IC9040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1846.3
2.5°	1804.0
5°	1766.2
7.5°	1747.7
10°	1739.5
12.5°	1712.0
15°	1657.1
17.5°	1569.9
20°	1445.4
22.5°	1301.8
25°	1152.1
27.5°	996.4
30°	831.6
32.5°	692.1
35°	570.4
37.5°	454.6
40°	341.4
42.5°	236.6
45°	143.9
47.5°	77.6
50°	42.8
52.5°	25.4
55°	16.5
57.5°	10.5
60°	6.2
62.5°	2.8
65°	0.7
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)