

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780169

Luminaire Tested: LER4D20D010-EC4DR2520359050-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR2520359050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1859.3 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780169

CATALOG NUMBER: LER4D20D010-EC4DR2520359050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780169

CATALOG NUMBER: LER4D20D010-EC4DR2520359050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109	112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101	109	105	102	100		102	100	98		99	97	96		97	95	94
3	107	102	98	95	105	101	97	94		98	95	93		96	93	91		94	92	90
4	103	97	93	90	102	96	93	90		94	91	89		93	90	88		91	89	87
5	100	93	89	86	98	93	89	86		91	87	85		89	86	84		88	85	83
6	97	90	85	82	95	89	85	82		88	84	81		87	83	81		85	83	80
7	93	87	82	79	92	86	82	79		85	81	78		84	80	78		83	80	78
8	91	84	79	76	90	83	79	76		82	78	76		81	78	75		80	77	75
9	88	81	76	73	87	80	76	73		80	76	73		79	75	73		78	75	73
10	85	78	74	71	85	78	74	71		77	73	71		76	73	71		76	73	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	770496
5°	717624
10°	511906
15°	301486
20°	187595
25°	102955
30°	47084
35°	17833
40°	8073
45°	4852
50°	2023
55°	1295
60°	896
65°	595
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4852 cd/sqm



TEST NUMBER: P780169

CATALOG NUMBER: LER4D20D010-EC4DR2520359050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	562.3	30.2
10°-20°	761.6	41.0
20°-30°	403.1	21.7
30°-40°	99.5	5.4
40°-50°	24.3	1.3
50°-60°	6.4	0.3
60°-70°	2.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1727.0	92.9
0°-40°	1826.5	98.2
0°-60°	1857.1	99.9
0°-90°	1859.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1859.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7052	
5°	6543	562
15°	2665	762
25°	854	403
35°	134	100
45°	31	24
55°	7	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780169

CATALOG NUMBER: LER4D20D010-EC4DR2520359050-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7051.9
2.5°	6936.0
5°	6543.0
7.5°	5753.3
10°	4614.0
12.5°	3487.9
15°	2665.3
17.5°	2077.2
20°	1613.4
22.5°	1210.0
25°	854.0
27.5°	572.7
30°	373.2
32.5°	227.1
35°	133.7
37.5°	81.8
40°	56.6
42.5°	43.3
45°	31.4
47.5°	19.0
50°	11.9
52.5°	8.6
55°	6.8
57.5°	5.3
60°	4.1
62.5°	3.3
65°	2.3
67.5°	0.9
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)