

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780497

Luminaire Tested: LER4D25D010-EC4DR3520359035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR3520359035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2529.1 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780497

CATALOG NUMBER: LER4D25D010-EC4DR3520359035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780497

CATALOG NUMBER: LER4D25D010-EC4DR3520359035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	760335
5°	742466
10°	669161
15°	519379
20°	294577
25°	114600
30°	42757
35°	23435
40°	15318
45°	9317
50°	5932
55°	4191
60°	3059
65°	1680
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9317 cd/sqm



TEST NUMBER: P780497

CATALOG NUMBER: LER4D25D010-EC4DR3520359035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	622.6	24.6
10°-20°	1215.6	48.1
20°-30°	495.8	19.6
30°-40°	118.6	4.7
40°-50°	49.4	2.0
50°-60°	20.4	0.8
60°-70°	6.4	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2333.9	92.3
0°-40°	2452.5	97.0
0°-60°	2522.4	99.7
0°-90°	2529.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2529.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6959	
5°	6770	623
15°	4592	1216
25°	951	496
35°	176	119
45°	60	49
55°	22	20
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780497

CATALOG NUMBER: LER4D25D010-EC4DR3520359035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6958.9
2.5°	6917.1
5°	6769.5
7.5°	6475.0
10°	6031.4
12.5°	5406.7
15°	4591.6
17.5°	3594.6
20°	2533.5
22.5°	1615.5
25°	950.6
27.5°	537.4
30°	338.9
32.5°	237.9
35°	175.7
37.5°	135.8
40°	107.4
42.5°	82.7
45°	60.3
47.5°	45.1
50°	34.9
52.5°	27.7
55°	22.0
57.5°	17.8
60°	14.0
62.5°	10.3
65°	6.5
67.5°	2.3
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)