

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780501

Luminaire Tested: LER4D25D010-EC4DR3520359040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR3520359040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2599.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780501

CATALOG NUMBER: LER4D25D010-EC4DR3520359040-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P780501

CATALOG NUMBER: LER4D25D010-EC4DR3520359040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	781356
5°	762998
10°	687656
15°	533733
20°	302728
25°	117771
30°	43930
35°	24089
40°	15746
45°	9580
50°	6102
55°	4305
60°	3147
65°	1706
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9580 cd/sqm

TEST NUMBER: P780501

CATALOG NUMBER: LER4D25D010-EC4DR3520359040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	639.8	24.6
10°-20°	1249.2	48.1
20°-30°	509.5	19.6
30°-40°	121.9	4.7
40°-50°	50.8	2.0
50°-60°	21.0	0.8
60°-70°	6.6	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2398.4	92.3
0°-40°	2520.4	97.0
0°-60°	2592.2	99.7
0°-90°	2599.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2599.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7151	
5°	6957	640
15°	4718	1249
25°	977	509
35°	181	122
45°	62	51
55°	23	21
65°	7	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780501

CATALOG NUMBER: LER4D25D010-EC4DR3520359040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7151.3
2.5°	7108.4
5°	6956.7
7.5°	6654.0
10°	6198.1
12.5°	5556.2
15°	4718.5
17.5°	3694.0
20°	2603.6
22.5°	1660.2
25°	976.9
27.5°	552.2
30°	348.2
32.5°	244.5
35°	180.6
37.5°	139.6
40°	110.4
42.5°	85.0
45°	62.0
47.5°	46.4
50°	35.9
52.5°	28.5
55°	22.6
57.5°	18.3
60°	14.4
62.5°	10.5
65°	6.6
67.5°	2.3
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)