

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780325

Luminaire Tested: LER4D20D010-EC4DR6020359030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6020359030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1946.5 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780325

CATALOG NUMBER: LER4D20D010-EC4DR6020359030-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P780325

CATALOG NUMBER: LER4D20D010-EC4DR6020359030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63	82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212829
5°	212315
10°	219374
15°	219590
20°	202047
25°	171852
30°	130945
35°	92594
40°	54370
45°	21942
50°	7326
55°	3524
60°	1442
65°	207
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21942 cd/sqm



TEST NUMBER: P780325

CATALOG NUMBER: LER4D20D010-EC4DR6020359030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.7	9.6
10°-20°	537.8	27.6
20°-30°	643.7	33.1
30°-40°	430.5	22.1
40°-50°	127.7	6.6
50°-60°	18.4	0.9
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1368.2	70.3
0°-40°	1798.8	92.4
0°-60°	1944.8	99.9
0°-90°	1946.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1946.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1948	
5°	1936	187
15°	1941	538
25°	1426	644
35°	694	431
45°	142	128
55°	18	18
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780325

CATALOG NUMBER: LER4D20D010-EC4DR6020359030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1947.9
2.5°	1945.5
5°	1935.8
7.5°	1962.0
10°	1977.3
12.5°	1974.4
15°	1941.3
17.5°	1863.1
20°	1737.7
22.5°	1587.1
25°	1425.5
27.5°	1243.5
30°	1037.9
32.5°	854.5
35°	694.2
37.5°	533.8
40°	381.2
42.5°	251.4
45°	142.0
47.5°	72.7
50°	43.1
52.5°	27.9
55°	18.5
57.5°	11.9
60°	6.6
62.5°	2.8
65°	0.8
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report







(END OF REPORT)