

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780341

Luminaire Tested: LER4D20D010-EC4DR6520359024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6520359024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1483.9 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780341

CATALOG NUMBER: LER4D20D010-EC4DR6520359024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780341

CATALOG NUMBER: LER4D20D010-EC4DR6520359024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78688
5°	78490
10°	78419
15°	76003
20°	69188
25°	60298
30°	50148
35°	39734
40°	28674
45°	18121
50°	9440
55°	5020
60°	2640
65°	1451
70°	615
75°	677
80°	471
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm



TEST NUMBER: P780341

CATALOG NUMBER: LER4D20D010-EC4DR6520359024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.4	8.6
10°-20°	348.9	23.5
20°-30°	426.5	28.7
30°-40°	346.0	23.3
40°-50°	172.4	11.6
50°-60°	48.1	3.2
60°-70°	10.9	0.7
70°-80°	2.9	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	902.8	60.8
0°-40°	1248.8	84.2
0°-60°	1469.4	99.0
0°-90°	1483.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1483.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1347	
5°	1339	127
15°	1257	349
25°	936	426
35°	557	346
45°	219	172
55°	49	48
65°	10	11
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P780341

CATALOG NUMBER: LER4D20D010-EC4DR6520359024-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1347.3
2.5°	1346.3
5°	1338.8
7.5°	1334.4
10°	1322.3
12.5°	1297.8
15°	1257.0
17.5°	1193.2
20°	1113.2
22.5°	1027.0
25°	935.7
27.5°	838.1
30°	743.6
32.5°	650.4
35°	557.3
37.5°	464.5
40°	376.1
42.5°	293.4
45°	219.4
47.5°	152.9
50°	103.9
52.5°	71.7
55°	49.3
57.5°	33.3
60°	22.6
62.5°	15.6
65°	10.5
67.5°	5.3
70°	3.6
72.5°	3.4
75°	3.0
77.5°	2.0
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)