

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780533

Luminaire Tested: LER4D25D010-EC4DR4520359024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR4520359024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2241.2 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780533

CATALOG NUMBER: LER4D25D010-EC4DR4520359024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780533

CATALOG NUMBER: LER4D25D010-EC4DR4520359024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		98	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91		103	98	94	91		95	92	89		93	90	88		91	89	87
4	100	94	89	85		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	83	80		86	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	75	72		87	80	75	72		79	74	71		78	74	71		77	73	71
8	85	77	72	68		84	76	71	68		75	71	68		74	70	67		73	70	67
9	82	73	68	65		81	73	68	65		72	68	65		71	67	64		71	67	64
10	79	70	65	62		78	70	65	62		69	65	62		68	64	61		68	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	432826
5°	420506
10°	402302
15°	368190
20°	292112
25°	182365
30°	100514
35°	45137
40°	17772
45°	8375
50°	3978
55°	2076
60°	1027
65°	233
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8375 cd/sqm



TEST NUMBER: P780533

CATALOG NUMBER: LER4D25D010-EC4DR4520359024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.2	16.1
10°-20°	886.6	39.6
20°-30°	702.1	31.3
30°-40°	233.8	10.4
40°-50°	46.4	2.1
50°-60°	10.6	0.5
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1948.9	87.0
0°-40°	2182.7	97.4
0°-60°	2239.7	99.9
0°-90°	2241.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2241.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3961	
5°	3834	360
15°	3255	887
25°	1513	702
35°	338	234
45°	54	46
55°	11	11
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780533

CATALOG NUMBER: LER4D25D010-EC4DR4520359024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3961.4
2.5°	3935.5
5°	3834.0
7.5°	3750.1
10°	3626.1
12.5°	3461.0
15°	3255.0
17.5°	2945.4
20°	2512.3
22.5°	1996.3
25°	1512.7
27.5°	1107.7
30°	796.7
32.5°	541.8
35°	338.4
37.5°	200.6
40°	124.6
42.5°	81.9
45°	54.2
47.5°	34.9
50°	23.4
52.5°	15.6
55°	10.9
57.5°	7.2
60°	4.7
62.5°	2.5
65°	0.9
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)