

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780574

Luminaire Tested: LER4D25D010-EC4DR5020359040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR5020359040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2963.9 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780574

CATALOG NUMBER: LER4D25D010-EC4DR5020359040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P780574

CATALOG NUMBER: LER4D25D010-EC4DR5020359040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521775
5°	516310
10°	507801
15°	462392
20°	384770
25°	273131
30°	144558
35°	58915
40°	21879
45°	10013
50°	4114
55°	2153
60°	1049
65°	310
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10013 cd/sqm



TEST NUMBER: P780574

CATALOG NUMBER: LER4D25D010-EC4DR5020359040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	445.0	15.0
10°-20°	1124.5	37.9
20°-30°	1010.1	34.1
30°-40°	316.2	10.7
40°-50°	55.4	1.9
50°-60°	11.1	0.4
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2579.5	87.0
0°-40°	2895.8	97.7
0°-60°	2962.2	99.9
0°-90°	2963.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2963.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4776	
5°	4708	445
15°	4088	1124
25°	2266	1010
35°	442	316
45°	65	55
55°	11	11
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780574

CATALOG NUMBER: LER4D25D010-EC4DR5020359040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4775.5
2.5°	4751.8
5°	4707.5
7.5°	4639.9
10°	4577.0
12.5°	4375.7
15°	4087.8
17.5°	3722.3
20°	3309.2
22.5°	2831.2
25°	2265.6
27.5°	1665.7
30°	1145.8
32.5°	746.0
35°	441.7
37.5°	253.6
40°	153.4
42.5°	99.9
45°	64.8
47.5°	39.5
50°	24.2
52.5°	16.5
55°	11.3
57.5°	7.7
60°	4.8
62.5°	2.8
65°	1.2
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)