

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780347

Luminaire Tested: LER4D20D010-EC4DR6520359027-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6520359027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1565.2 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780347

CATALOG NUMBER: LER4D20D010-EC4DR6520359027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P780347

CATALOG NUMBER: LER4D20D010-EC4DR6520359027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82998
5°	82793
10°	82718
15°	80169
20°	72985
25°	63604
30°	52899
35°	41916
40°	30252
45°	19113
50°	9967
55°	5295
60°	2780
65°	1534
70°	649
75°	722
80°	505
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19113 cd/sqm



TEST NUMBER: P780347

CATALOG NUMBER: LER4D20D010-EC4DR6520359027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	8.6
10°-20°	368.0	23.5
20°-30°	449.9	28.7
30°-40°	365.0	23.3
40°-50°	181.9	11.6
50°-60°	50.7	3.2
60°-70°	11.5	0.7
70°-80°	3.0	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.3	60.8
0°-40°	1317.3	84.2
0°-60°	1549.9	99.0
0°-90°	1565.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1565.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1421	
5°	1412	134
15°	1326	368
25°	987	450
35°	588	365
45°	231	182
55°	52	51
65°	11	12
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P780347

CATALOG NUMBER: LER4D20D010-EC4DR6520359027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1421.1
2.5°	1420.1
5°	1412.2
7.5°	1407.6
10°	1394.8
12.5°	1369.0
15°	1325.9
17.5°	1258.7
20°	1174.3
22.5°	1083.2
25°	987.0
27.5°	884.0
30°	784.4
32.5°	686.1
35°	587.9
37.5°	489.9
40°	396.8
42.5°	309.5
45°	231.4
47.5°	161.2
50°	109.7
52.5°	75.6
55°	52.0
57.5°	35.1
60°	23.8
62.5°	16.5
65°	11.1
67.5°	5.6
70°	3.8
72.5°	3.6
75°	3.2
77.5°	2.1
80°	1.5
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)