

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780357

Luminaire Tested: LER4D20D010-EC4DR6520359040-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6520359040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1845.1 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780357

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780357

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97850
5°	97602
10°	97515
15°	94511
20°	86043
25°	74978
30°	62361
35°	49409
40°	35665
45°	22532
50°	11748
55°	6242
60°	3282
65°	1810
70°	751
75°	835
80°	572
85°	469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22532 cd/sqm



TEST NUMBER: P780357

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	8.6
10°-20°	433.9	23.5
20°-30°	530.3	28.7
30°-40°	430.3	23.3
40°-50°	214.4	11.6
50°-60°	59.8	3.2
60°-70°	13.6	0.7
70°-80°	3.5	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.6	60.8
0°-40°	1552.9	84.2
0°-60°	1827.1	99.0
0°-90°	1845.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1845.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1675	
5°	1665	158
15°	1563	434
25°	1164	530
35°	693	430
45°	273	214
55°	61	60
65°	13	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P780357

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1675.4
2.5°	1674.1
5°	1664.8
7.5°	1659.3
10°	1644.3
12.5°	1613.8
15°	1563.1
17.5°	1483.8
20°	1384.4
22.5°	1277.0
25°	1163.5
27.5°	1042.1
30°	924.7
32.5°	808.7
35°	693.0
37.5°	577.6
40°	467.8
42.5°	364.9
45°	272.8
47.5°	190.0
50°	129.3
52.5°	89.1
55°	61.3
57.5°	41.4
60°	28.1
62.5°	19.4
65°	13.1
67.5°	6.6
70°	4.4
72.5°	4.2
75°	3.7
77.5°	2.5
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)