

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780358

Luminaire Tested: LER4D20D010-EC4DR6520359040-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D20D010-EC4DR6520359040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1937.4 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780358

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P780358

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102738
5°	102480
10°	102390
15°	99234
20°	90344
25°	78728
30°	65477
35°	51884
40°	37442
45°	23655
50°	12330
55°	6547
60°	3434
65°	1893
70°	786
75°	880
80°	605
85°	536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23655 cd/sqm



TEST NUMBER: P780358

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.4	8.6
10°-20°	455.5	23.5
20°-30°	556.8	28.7
30°-40°	451.8	23.3
40°-50°	225.1	11.6
50°-60°	62.8	3.2
60°-70°	14.3	0.7
70°-80°	3.7	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.7	60.8
0°-40°	1630.5	84.2
0°-60°	1918.4	99.0
0°-90°	1937.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1937.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1759	
5°	1748	166
15°	1641	456
25°	1222	557
35°	728	452
45°	286	225
55°	64	63
65°	14	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P780358

CATALOG NUMBER: LER4D20D010-EC4DR6520359040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1759.1
2.5°	1757.8
5°	1748.0
7.5°	1742.3
10°	1726.5
12.5°	1694.5
15°	1641.2
17.5°	1558.0
20°	1453.6
22.5°	1340.9
25°	1221.7
27.5°	1094.2
30°	970.9
32.5°	849.2
35°	727.7
37.5°	606.5
40°	491.1
42.5°	383.1
45°	286.4
47.5°	199.6
50°	135.7
52.5°	93.6
55°	64.3
57.5°	43.4
60°	29.4
62.5°	20.4
65°	13.7
67.5°	7.0
70°	4.6
72.5°	4.4
75°	3.9
77.5°	2.6
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)