

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780629

Luminaire Tested: LER4D25D010-EC4DR6520359024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P780629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR6520359024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1917.5 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780629

CATALOG NUMBER: LER4D25D010-EC4DR6520359024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P780629

CATALOG NUMBER: LER4D25D010-EC4DR6520359024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	97	95	94	93	93				
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78				
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72				
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66				
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61				
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56				
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52				
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49				
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101681
5°	101425
10°	101340
15°	98212
20°	89412
25°	77916
30°	64809
35°	51349
40°	37061
45°	23416
50°	12203
55°	6486
60°	3411
65°	1879
70°	786
75°	857
80°	605
85°	469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23416 cd/sqm



TEST NUMBER: P780629

CATALOG NUMBER: LER4D25D010-EC4DR6520359024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.6	8.6
10°-20°	450.8	23.5
20°-30°	551.1	28.7
30°-40°	447.2	23.3
40°-50°	222.8	11.6
50°-60°	62.2	3.2
60°-70°	14.1	0.7
70°-80°	3.7	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1166.6	60.8
0°-40°	1613.8	84.2
0°-60°	1898.7	99.0
0°-90°	1917.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1917.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1741	
5°	1730	165
15°	1624	451
25°	1209	551
35°	720	447
45°	284	223
55°	64	62
65°	14	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P780629

CATALOG NUMBER: LER4D25D010-EC4DR6520359024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1741.0
2.5°	1739.7
5°	1730.0
7.5°	1724.4
10°	1708.8
12.5°	1677.0
15°	1624.3
17.5°	1541.9
20°	1438.6
22.5°	1327.0
25°	1209.1
27.5°	1083.0
30°	961.0
32.5°	840.5
35°	720.2
37.5°	600.2
40°	486.1
42.5°	379.2
45°	283.5
47.5°	197.5
50°	134.3
52.5°	92.6
55°	63.7
57.5°	43.0
60°	29.2
62.5°	20.2
65°	13.6
67.5°	6.9
70°	4.6
72.5°	4.4
75°	3.8
77.5°	2.6
80°	1.8
82.5°	1.3
85°	0.7
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)