

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780495

Luminaire Tested: LER4D25D010-EC4DR3520359030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR3520359030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2277.4 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780495

CATALOG NUMBER: LER4D25D010-EC4DR3520359030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P780495

CATALOG NUMBER: LER4D25D010-EC4DR3520359030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	684650
5°	668565
10°	602560
15°	467674
20°	265265
25°	103196
30°	38505
35°	21101
40°	13792
45°	8390
50°	5354
55°	3772
60°	2775
65°	1499
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8390 cd/sqm



TEST NUMBER: P780495

CATALOG NUMBER: LER4D25D010-EC4DR3520359030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	560.6	24.6
10°-20°	1094.6	48.1
20°-30°	446.4	19.6
30°-40°	106.8	4.7
40°-50°	44.5	2.0
50°-60°	18.4	0.8
60°-70°	5.8	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2101.6	92.3
0°-40°	2208.4	97.0
0°-60°	2271.4	99.7
0°-90°	2277.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2277.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6266	
5°	6096	561
15°	4134	1095
25°	856	446
35°	158	107
45°	54	45
55°	20	18
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780495

CATALOG NUMBER: LER4D25D010-EC4DR3520359030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6266.2
2.5°	6228.6
5°	6095.7
7.5°	5830.5
10°	5431.1
12.5°	4868.6
15°	4134.5
17.5°	3236.8
20°	2281.4
22.5°	1454.7
25°	856.0
27.5°	483.9
30°	305.2
32.5°	214.3
35°	158.2
37.5°	122.3
40°	96.7
42.5°	74.5
45°	54.3
47.5°	40.7
50°	31.5
52.5°	24.9
55°	19.8
57.5°	16.0
60°	12.7
62.5°	9.2
65°	5.8
67.5°	2.1
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)