

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780974

Luminaire Tested: LER4D35BD010-EC4DR2520359030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P780974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR2520359030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3155.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P780974

CATALOG NUMBER: LER4D35BD010-EC4DR2520359030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P780974

CATALOG NUMBER: LER4D35BD010-EC4DR2520359030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1307808
5°	1218063
10°	868876
15°	511733
20°	318413
25°	174746
30°	79912
35°	30265
40°	13707
45°	8236
50°	3417
55°	2210
60°	1530
65°	1034
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8236 cd/sqm



TEST NUMBER: P780974

CATALOG NUMBER: LER4D35BD010-EC4DR2520359030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	954.5	30.2
10°-20°	1292.7	41.0
20°-30°	684.1	21.7
30°-40°	168.9	5.4
40°-50°	41.2	1.3
50°-60°	10.9	0.3
60°-70°	3.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2931.3	92.9
0°-40°	3100.2	98.2
0°-60°	3152.2	99.9
0°-90°	3155.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3155.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11970	
5°	11106	954
15°	4524	1293
25°	1450	684
35°	227	169
45°	53	41
55°	12	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780974

CATALOG NUMBER: LER4D35BD010-EC4DR2520359030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11969.6
2.5°	11772.9
5°	11105.8
7.5°	9765.5
10°	7831.5
12.5°	5920.2
15°	4524.0
17.5°	3525.8
20°	2738.5
22.5°	2053.7
25°	1449.5
27.5°	972.0
30°	633.4
32.5°	385.4
35°	226.9
37.5°	138.9
40°	96.1
42.5°	73.5
45°	53.3
47.5°	32.2
50°	20.1
52.5°	14.6
55°	11.6
57.5°	9.1
60°	7.0
62.5°	5.5
65°	4.0
67.5°	1.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)