

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P780660

Luminaire Tested: LER4D25D010-EC4DR7020359030-4LBS1B

Issue Date: 1/31/2024

Test Information

Test Method: LM-79-2019
Report Number: P780660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/31/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D25D010-EC4DR7020359030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2356.6 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P780660

CATALOG NUMBER: LER4D25D010-EC4DR7020359030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P780660

CATALOG NUMBER: LER4D25D010-EC4DR7020359030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	76		93	86	80	76		83	78	75		81	77	74		79	76	73
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67
6	84	75	68	63		83	74	68	63		72	67	63		71	66	62		69	65	62
7	80	69	63	58		78	69	63	58		67	62	58		66	61	57		65	61	57
8	75	65	58	54		74	64	58	54		63	57	53		62	57	53		61	56	53
9	71	61	54	50		70	60	54	50		59	53	50		58	53	49		57	53	49
10	67	57	50	46		66	56	50	46		55	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203236
5°	202729
10°	202288
15°	202227
20°	200257
25°	188115
30°	167696
35°	133703
40°	88787
45°	53077
50°	27520
55°	14458
60°	5113
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53077 cd/sqm



TEST NUMBER: P780660

CATALOG NUMBER: LER4D25D010-EC4DR7020359030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.8	7.5
10°-20°	504.1	21.4
20°-30°	711.2	30.2
30°-40°	613.9	26.1
40°-50°	274.9	11.7
50°-60°	72.0	3.1
60°-70°	4.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1391.1	59.0
0°-40°	2005.1	85.1
0°-60°	2352.0	99.8
0°-90°	2356.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2356.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1860	
5°	1848	176
15°	1788	504
25°	1560	711
35°	1002	614
45°	344	275
55°	76	72
65°	0	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P780660

CATALOG NUMBER: LER4D25D010-EC4DR7020359030-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1860.1
2.5°	1858.1
5°	1848.4
7.5°	1840.4
10°	1823.3
12.5°	1807.9
15°	1787.8
17.5°	1764.7
20°	1722.3
22.5°	1652.4
25°	1560.4
27.5°	1453.7
30°	1329.2
32.5°	1177.1
35°	1002.4
37.5°	809.8
40°	622.5
42.5°	473.0
45°	343.5
47.5°	236.8
50°	161.9
52.5°	111.7
55°	75.9
57.5°	45.8
60°	23.4
62.5°	7.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)