

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781146

Luminaire Tested: LER4D35BD010-EC4DR6020359035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR6020359035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3579.3 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781146

CATALOG NUMBER: LER4D35BD010-EC4DR6020359035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781146

CATALOG NUMBER: LER4D35BD010-EC4DR6020359035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391372
5°	390410
10°	403378
15°	403798
20°	371538
25°	316013
30°	240796
35°	170276
40°	99998
45°	40345
50°	13462
55°	6477
60°	2666
65°	388
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40345 cd/sqm



TEST NUMBER: P781146

CATALOG NUMBER: LER4D35BD010-EC4DR6020359035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.4	9.6
10°-20°	989.0	27.6
20°-30°	1183.7	33.1
30°-40°	791.7	22.1
40°-50°	234.7	6.6
50°-60°	33.7	0.9
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2516.0	70.3
0°-40°	3307.7	92.4
0°-60°	3576.1	99.9
0°-90°	3579.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3579.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3582	
5°	3560	343
15°	3570	989
25°	2621	1184
35°	1277	792
45°	261	235
55°	34	34
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781146

CATALOG NUMBER: LER4D35BD010-EC4DR6020359035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3582.0
2.5°	3577.4
5°	3559.6
7.5°	3607.9
10°	3635.8
12.5°	3630.8
15°	3569.8
17.5°	3426.0
20°	3195.4
22.5°	2918.5
25°	2621.3
27.5°	2286.6
30°	1908.6
32.5°	1571.3
35°	1276.6
37.5°	981.5
40°	701.1
42.5°	462.3
45°	261.1
47.5°	133.6
50°	79.2
52.5°	51.3
55°	34.0
57.5°	21.8
60°	12.2
62.5°	5.1
65°	1.5
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)