

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781023

Luminaire Tested: LER4D35BD010-EC4DR3520359030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR3520359030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3054.3 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781023

CATALOG NUMBER: LER4D35BD010-EC4DR3520359030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781023

CATALOG NUMBER: LER4D35BD010-EC4DR3520359030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	918206
5°	896630
10°	808099
15°	627212
20°	355748
25°	138398
30°	51639
35°	28304
40°	18499
45°	11264
50°	7173
55°	5067
60°	3715
65°	2017
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11264 cd/sqm



TEST NUMBER: P781023

CATALOG NUMBER: LER4D35BD010-EC4DR3520359030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.9	24.6
10°-20°	1468.0	48.1
20°-30°	598.7	19.6
30°-40°	143.3	4.7
40°-50°	59.7	2.0
50°-60°	24.7	0.8
60°-70°	7.7	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2818.5	92.3
0°-40°	2961.8	97.0
0°-60°	3046.3	99.7
0°-90°	3054.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3054.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8404	
5°	8175	752
15°	5545	1468
25°	1148	599
35°	212	143
45°	73	60
55°	27	25
65°	8	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781023

CATALOG NUMBER: LER4D35BD010-EC4DR3520359030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8403.8
2.5°	8353.4
5°	8175.1
7.5°	7819.5
10°	7283.7
12.5°	6529.4
15°	5544.9
17.5°	4341.0
20°	3059.6
22.5°	1951.0
25°	1148.0
27.5°	649.0
30°	409.3
32.5°	287.4
35°	212.2
37.5°	164.1
40°	129.7
42.5°	99.9
45°	72.9
47.5°	54.5
50°	42.2
52.5°	33.5
55°	26.6
57.5°	21.5
60°	17.0
62.5°	12.4
65°	7.8
67.5°	2.7
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)