

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781035

Luminaire Tested: LER4D35BD010-EC4DR3520359050-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR3520359050-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3253.8 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781035

CATALOG NUMBER: LER4D35BD010-EC4DR3520359050-4LBS1MW

Luminous Intensity Polar Plot



CATALOG NUMBER: LER4D35BD010-EC4DR3520359050-4LBS1MW

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

	0°
0°	978201
5°	955209
10°	860899
15°	668193
20°	378991
25°	147440
30°	55007
35°	30158
40°	19711
45°	11991
50°	7632
55°	5391
60°	3955
65°	2146
70°	160
75°	0
80°	0
85°	0

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11991 cd/sqm



TEST NUMBER: P781035

CATALOG NUMBER: LER4D35BD010-EC4DR3520359050-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	801.0	24.6
10°-20°	1563.9	48.1
20°-30°	637.8	19.6
30°-40°	152.6	4.7
40°-50°	63.6	2.0
50°-60°	26.3	0.8
60°-70°	8.2	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3002.7	92.3
0°-40°	3155.3	97.0
0°-60°	3245.2	99.7
0°-90°	3253.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3253.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8953	
5°	8709	801
15°	5907	1564
25°	1223	638
35°	226	153
45°	78	64
55°	28	26
65°	8	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781035

CATALOG NUMBER: LER4D35BD010-EC4DR3520359050-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8952.9
2.5°	8899.2
5°	8709.2
7.5°	8330.4
10°	7759.6
12.5°	6956.0
15°	5907.2
17.5°	4624.6
20°	3259.5
22.5°	2078.4
25°	1223.0
27.5°	691.3
30°	436.0
32.5°	306.1
35°	226.1
37.5°	174.8
40°	138.2
42.5°	106.4
45°	77.6
47.5°	58.1
50°	44.9
52.5°	35.6
55°	28.3
57.5°	22.9
60°	18.1
62.5°	13.2
65°	8.3
67.5°	2.9
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)