

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781179

Luminaire Tested: LER4D35BD010-EC4DR6520359050-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR6520359050-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2983.9 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781179

CATALOG NUMBER: LER4D35BD010-EC4DR6520359050-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781179

CATALOG NUMBER: LER4D35BD010-EC4DR6520359050-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158228
5°	157830
10°	157698
15°	152835
20°	139134
25°	121247
30°	100848
35°	79904
40°	57669
45°	36433
50°	18990
55°	10091
60°	5303
65°	2916
70°	1229
75°	1354
80°	942
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36433 cd/sqm



TEST NUMBER: P781179

CATALOG NUMBER: LER4D35BD010-EC4DR6520359050-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.2	8.6
10°-20°	701.6	23.5
20°-30°	857.6	28.7
30°-40°	695.8	23.3
40°-50°	346.7	11.6
50°-60°	96.7	3.2
60°-70°	22.0	0.7
70°-80°	5.7	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1815.4	60.8
0°-40°	2511.2	84.2
0°-60°	2954.7	99.0
0°-90°	2983.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2983.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2709	
5°	2692	256
15°	2528	702
25°	1882	858
35°	1121	696
45°	441	347
55°	99	97
65°	21	22
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P781179

CATALOG NUMBER: LER4D35BD010-EC4DR6520359050-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2709.2
2.5°	2707.2
5°	2692.1
7.5°	2683.4
10°	2659.1
12.5°	2609.7
15°	2527.7
17.5°	2399.5
20°	2238.6
22.5°	2065.1
25°	1881.5
27.5°	1685.3
30°	1495.4
32.5°	1307.8
35°	1120.7
37.5°	934.0
40°	756.4
42.5°	590.0
45°	441.1
47.5°	307.4
50°	209.0
52.5°	144.1
55°	99.1
57.5°	66.9
60°	45.4
62.5°	31.5
65°	21.1
67.5°	10.7
70°	7.2
72.5°	6.8
75°	6.0
77.5°	4.0
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)