

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781041

Luminaire Tested: LER4D35BD010-EC4DR4020359027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR4020359027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3408.6 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781041

CATALOG NUMBER: LER4D35BD010-EC4DR4020359027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781041

CATALOG NUMBER: LER4D35BD010-EC4DR4020359027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	97
2	110	106	103	100	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	104	100	96	93		97	94	92		95	93	90		93	91	89
4	102	97	92	89	101	95	91	88		93	90	87		92	89	86		90	87	85
5	99	92	88	84	97	91	87	84		90	86	83		88	85	83		87	84	82
6	95	88	84	80	94	88	83	80		86	82	80		85	82	79		84	81	79
7	92	85	80	77	91	84	80	77		83	79	76		82	79	76		81	78	76
8	89	82	77	74	88	81	77	74		80	76	73		79	76	73		78	75	73
9	86	79	74	71	85	78	74	71		77	73	71		76	73	70		76	72	70
10	83	76	71	68	82	75	71	68		75	71	68		74	70	68		73	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	867115
5°	862893
10°	815622
15°	693384
20°	472591
25°	197181
30°	61997
35°	28811
40°	15932
45°	7309
50°	3553
55°	1943
60°	1005
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7309 cd/sqm



TEST NUMBER: P781041

CATALOG NUMBER: LER4D35BD010-EC4DR4020359027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	734.6	21.6
10°-20°	1645.8	48.3
20°-30°	823.8	24.2
30°-40°	151.0	4.4
40°-50°	41.7	1.2
50°-60°	9.8	0.3
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3204.2	94.0
0°-40°	3355.2	98.4
0°-60°	3406.6	99.9
0°-90°	3408.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3408.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7936	
5°	7868	735
15°	6130	1646
25°	1636	824
35°	216	151
45°	47	42
55°	10	10
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781041

CATALOG NUMBER: LER4D35BD010-EC4DR4020359027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7936.2
2.5°	7924.6
5°	7867.5
7.5°	7685.8
10°	7351.5
12.5°	6830.4
15°	6129.9
17.5°	5218.9
20°	4064.5
22.5°	2771.0
25°	1635.6
27.5°	864.6
30°	491.4
32.5°	317.6
35°	216.0
37.5°	154.4
40°	111.7
42.5°	76.5
45°	47.3
47.5°	30.1
50°	20.9
52.5°	14.8
55°	10.2
57.5°	6.5
60°	4.6
62.5°	2.8
65°	1.4
67.5°	0.9
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)