

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781189

Luminaire Tested: LER4D35BD010-EC4DR7020359030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR7020359030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3395.5 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781189

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781189

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	292819
5°	292095
10°	291456
15°	291373
20°	288531
25°	271034
30°	241628
35°	192645
40°	127925
45°	76471
50°	39656
55°	20840
60°	7364
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 76471 cd/sqm



TEST NUMBER: P781189

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.3	7.5
10°-20°	726.4	21.4
20°-30°	1024.7	30.2
30°-40°	884.6	26.1
40°-50°	396.1	11.7
50°-60°	103.7	3.1
60°-70°	6.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2004.3	59.0
0°-40°	2888.9	85.1
0°-60°	3388.8	99.8
0°-90°	3395.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3395.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2680	
5°	2663	253
15°	2576	726
25°	2248	1025
35°	1444	885
45°	495	396
55°	109	104
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781189

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2680.0
2.5°	2677.1
5°	2663.2
7.5°	2651.6
10°	2627.0
12.5°	2604.8
15°	2575.9
17.5°	2542.7
20°	2481.5
22.5°	2380.7
25°	2248.2
27.5°	2094.5
30°	1915.2
32.5°	1695.9
35°	1444.3
37.5°	1166.8
40°	896.9
42.5°	681.5
45°	494.9
47.5°	341.2
50°	233.3
52.5°	161.0
55°	109.4
57.5°	66.0
60°	33.7
62.5°	10.6
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)