

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781048

Luminaire Tested: LER4D35BD010-EC4DR4020359035-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR4020359035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3332.6 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781048

CATALOG NUMBER: LER4D35BD010-EC4DR4020359035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P781048

CATALOG NUMBER: LER4D35BD010-EC4DR4020359035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	97
2	110	106	103	100	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	104	100	96	93		97	94	92		95	93	90		93	91	89
4	102	97	92	89	101	95	91	88		93	90	87		92	89	86		90	87	85
5	99	92	88	84	97	91	87	84		90	86	83		88	85	83		87	84	82
6	95	88	84	80	94	88	83	80		86	82	80		85	82	79		84	81	79
7	92	85	80	77	91	84	80	77		83	79	76		82	79	76		81	78	76
8	89	82	77	74	88	81	77	74		80	76	73		79	76	73		78	75	73
9	86	79	74	71	85	78	74	71		77	73	71		76	73	70		76	72	70
10	83	76	71	68	82	75	71	68		75	71	68		74	70	68		73	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	847765
5°	843644
10°	797437
15°	677921
20°	462045
25°	192781
30°	60622
35°	28170
40°	15575
45°	7139
50°	3468
55°	1905
60°	983
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7139 cd/sqm



TEST NUMBER: P781048

CATALOG NUMBER: LER4D35BD010-EC4DR4020359035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	718.2	21.6
10°-20°	1609.1	48.3
20°-30°	805.4	24.2
30°-40°	147.6	4.4
40°-50°	40.7	1.2
50°-60°	9.6	0.3
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3132.7	94.0
0°-40°	3280.4	98.4
0°-60°	3330.7	99.9
0°-90°	3332.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3332.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7759	
5°	7692	718
15°	5993	1609
25°	1599	805
35°	211	148
45°	46	41
55°	10	10
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781048

CATALOG NUMBER: LER4D35BD010-EC4DR4020359035-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7759.1
2.5°	7747.8
5°	7692.0
7.5°	7514.4
10°	7187.6
12.5°	6678.1
15°	5993.2
17.5°	5102.5
20°	3973.8
22.5°	2709.2
25°	1599.1
27.5°	845.4
30°	480.5
32.5°	310.5
35°	211.2
37.5°	150.9
40°	109.2
42.5°	74.8
45°	46.2
47.5°	29.5
50°	20.4
52.5°	14.5
55°	10.0
57.5°	6.3
60°	4.5
62.5°	2.7
65°	1.4
67.5°	0.9
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)