

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781190

Luminaire Tested: LER4D35BD010-EC4DR7020359030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR7020359030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3565.3 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781190

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781190

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307460
5°	306693
10°	306034
15°	305942
20°	302949
25°	284584
30°	253715
35°	202288
40°	134314
45°	80303
50°	41628
55°	21887
60°	7736
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 80303 cd/sqm



TEST NUMBER: P781190

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.9	7.5
10°-20°	762.7	21.4
20°-30°	1075.9	30.2
30°-40°	928.8	26.1
40°-50°	415.9	11.7
50°-60°	108.9	3.1
60°-70°	7.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2104.5	59.0
0°-40°	3033.4	85.1
0°-60°	3558.2	99.8
0°-90°	3565.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3565.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2814	
5°	2796	266
15°	2705	763
25°	2361	1076
35°	1517	929
45°	520	416
55°	115	109
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781190

CATALOG NUMBER: LER4D35BD010-EC4DR7020359030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2814.0
2.5°	2811.0
5°	2796.3
7.5°	2784.2
10°	2758.4
12.5°	2735.1
15°	2704.7
17.5°	2669.8
20°	2605.5
22.5°	2499.8
25°	2360.6
27.5°	2199.2
30°	2011.0
32.5°	1780.7
35°	1516.6
37.5°	1225.1
40°	941.7
42.5°	715.5
45°	519.7
47.5°	358.3
50°	244.9
52.5°	169.0
55°	114.9
57.5°	69.3
60°	35.4
62.5°	11.1
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)