

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781197

Luminaire Tested: LER4D35BD010-EC4DR7020359040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR7020359040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3591.6 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781197

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781197

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309743
5°	308963
10°	308298
15°	308216
20°	305193
25°	286694
30°	255582
35°	203782
40°	135313
45°	80890
50°	41934
55°	22040
60°	7801
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 80890 cd/sqm



TEST NUMBER: P781197

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.9	7.5
10°-20°	768.3	21.4
20°-30°	1083.9	30.2
30°-40°	935.7	26.1
40°-50°	419.0	11.7
50°-60°	109.7	3.1
60°-70°	7.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2120.1	59.0
0°-40°	3055.8	85.1
0°-60°	3584.5	99.8
0°-90°	3591.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3591.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2835	
5°	2817	268
15°	2725	768
25°	2378	1084
35°	1528	936
45°	524	419
55°	116	110
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781197

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2834.9
2.5°	2831.8
5°	2817.0
7.5°	2804.8
10°	2778.8
12.5°	2755.3
15°	2724.8
17.5°	2689.6
20°	2624.8
22.5°	2518.3
25°	2378.1
27.5°	2215.5
30°	2025.8
32.5°	1793.9
35°	1527.8
37.5°	1234.2
40°	948.7
42.5°	720.8
45°	523.5
47.5°	360.9
50°	246.7
52.5°	170.3
55°	115.7
57.5°	69.8
60°	35.7
62.5°	11.2
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)