

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781112

Luminaire Tested: LER4D35BD010-EC4DR5520359027-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR5520359027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3133.6 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781112

CATALOG NUMBER: LER4D35BD010-EC4DR5520359027-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P781112

CATALOG NUMBER: LER4D35BD010-EC4DR5520359027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	383931
5°	368683
10°	367288
15°	356742
20°	319867
25°	264355
30°	199692
35°	144787
40°	92667
45°	42322
50°	13836
55°	5981
60°	2579
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42322 cd/sqm



TEST NUMBER: P781112

CATALOG NUMBER: LER4D35BD010-EC4DR5520359027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.9	10.2
10°-20°	873.0	27.9
20°-30°	994.8	31.7
30°-40°	677.2	21.6
40°-50°	233.4	7.4
50°-60°	32.3	1.0
60°-70°	3.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2187.7	69.8
0°-40°	2864.9	91.4
0°-60°	3130.5	99.9
0°-90°	3133.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3133.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3514	
5°	3362	320
15°	3154	873
25°	2193	995
35°	1086	677
45°	274	233
55°	31	32
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781112

CATALOG NUMBER: LER4D35BD010-EC4DR5520359027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3513.9
2.5°	3433.3
5°	3361.5
7.5°	3326.2
10°	3310.5
12.5°	3258.3
15°	3153.8
17.5°	2987.9
20°	2751.0
22.5°	2477.6
25°	2192.8
27.5°	1896.3
30°	1582.8
32.5°	1317.2
35°	1085.5
37.5°	865.2
40°	649.7
42.5°	450.2
45°	273.9
47.5°	147.6
50°	81.4
52.5°	48.3
55°	31.4
57.5°	20.0
60°	11.8
62.5°	5.2
65°	1.3
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)