

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781157

Luminaire Tested: LER4D35BD010-EC4DR6520359024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR6520359024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2525.8 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781157

CATALOG NUMBER: LER4D35BD010-EC4DR6520359024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781157

CATALOG NUMBER: LER4D35BD010-EC4DR6520359024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133938
5°	133599
10°	133483
15°	129369
20°	117778
25°	102636
30°	85364
35°	67640
40°	48817
45°	30841
50°	16073
55°	8543
60°	4485
65°	2474
70°	1042
75°	1151
80°	807
85°	670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30841 cd/sqm



TEST NUMBER: P781157

CATALOG NUMBER: LER4D35BD010-EC4DR6520359024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.9	8.6
10°-20°	593.9	23.5
20°-30°	725.9	28.7
30°-40°	589.0	23.3
40°-50°	293.5	11.6
50°-60°	81.9	3.2
60°-70°	18.6	0.7
70°-80°	4.9	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1536.7	60.8
0°-40°	2125.7	84.2
0°-60°	2501.0	99.0
0°-90°	2525.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2525.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2293	
5°	2279	217
15°	2140	594
25°	1593	726
35°	949	589
45°	373	294
55°	84	82
65°	18	19
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P781157

CATALOG NUMBER: LER4D35BD010-EC4DR6520359024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2293.3
2.5°	2291.6
5°	2278.8
7.5°	2271.4
10°	2250.8
12.5°	2209.0
15°	2139.6
17.5°	2031.1
20°	1895.0
22.5°	1748.0
25°	1592.7
27.5°	1426.5
30°	1265.8
32.5°	1107.0
35°	948.7
37.5°	790.6
40°	640.3
42.5°	499.4
45°	373.4
47.5°	260.2
50°	176.9
52.5°	122.0
55°	83.9
57.5°	56.6
60°	38.4
62.5°	26.6
65°	17.9
67.5°	9.1
70°	6.1
72.5°	5.7
75°	5.1
77.5°	3.4
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)