

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781258

Luminaire Tested: LER4D40BD010-EC4DR3540509027-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR3540509027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3855.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781258

CATALOG NUMBER: LER4D40BD010-EC4DR3540509027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781258

CATALOG NUMBER: LER4D40BD010-EC4DR3540509027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1158929
5°	1131692
10°	1019951
15°	791647
20°	449011
25°	174686
30°	65176
35°	35720
40°	23348
45°	14216
50°	9043
55°	6381
60°	4676
65°	2534
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14216 cd/sqm



TEST NUMBER: P781258

CATALOG NUMBER: LER4D40BD010-EC4DR3540509027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	949.0	24.6
10°-20°	1852.8	48.1
20°-30°	755.7	19.6
30°-40°	180.8	4.7
40°-50°	75.4	2.0
50°-60°	31.2	0.8
60°-70°	9.8	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3557.4	92.3
0°-40°	3738.3	97.0
0°-60°	3844.8	99.7
0°-90°	3855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10607	
5°	10318	949
15°	6999	1853
25°	1449	756
35°	268	181
45°	92	75
55°	34	31
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781258

CATALOG NUMBER: LER4D40BD010-EC4DR3540509027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10607.0
2.5°	10543.3
5°	10318.3
7.5°	9869.4
10°	9193.2
12.5°	8241.1
15°	6998.6
17.5°	5479.0
20°	3861.7
22.5°	2462.4
25°	1449.0
27.5°	819.1
30°	516.6
32.5°	362.7
35°	267.8
37.5°	207.1
40°	163.7
42.5°	126.1
45°	92.0
47.5°	68.8
50°	53.2
52.5°	42.2
55°	33.5
57.5°	27.2
60°	21.4
62.5°	15.6
65°	9.8
67.5°	3.5
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)