

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781165

Luminaire Tested: LER4D35BD010-EC4DR6520359030-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR6520359030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2947.6 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781165

CATALOG NUMBER: LER4D35BD010-EC4DR6520359030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781165

CATALOG NUMBER: LER4D35BD010-EC4DR6520359030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156306
5°	155913
10°	155776
15°	150979
20°	137443
25°	119777
30°	99621
35°	78934
40°	56967
45°	35995
50°	18763
55°	9969
60°	5233
65°	2874
70°	1212
75°	1331
80°	942
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35995 cd/sqm



TEST NUMBER: P781165

CATALOG NUMBER: LER4D35BD010-EC4DR6520359030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.1	8.6
10°-20°	693.1	23.5
20°-30°	847.2	28.7
30°-40°	687.3	23.3
40°-50°	342.5	11.6
50°-60°	95.5	3.2
60°-70°	21.7	0.7
70°-80°	5.7	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1793.3	60.8
0°-40°	2480.7	84.2
0°-60°	2918.7	99.0
0°-90°	2947.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2947.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2676	
5°	2659	253
15°	2497	693
25°	1859	847
35°	1107	687
45°	436	343
55°	98	96
65°	21	22
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P781165

CATALOG NUMBER: LER4D35BD010-EC4DR6520359030-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2676.3
2.5°	2674.3
5°	2659.4
7.5°	2650.7
10°	2626.7
12.5°	2578.0
15°	2497.0
17.5°	2370.3
20°	2211.4
22.5°	2040.0
25°	1858.7
27.5°	1664.8
30°	1477.2
32.5°	1291.9
35°	1107.1
37.5°	922.6
40°	747.2
42.5°	582.8
45°	435.8
47.5°	303.6
50°	206.5
52.5°	142.4
55°	97.9
57.5°	66.1
60°	44.8
62.5°	31.1
65°	20.8
67.5°	10.6
70°	7.1
72.5°	6.7
75°	5.9
77.5°	3.9
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)